

Interrupteur à bascule British Standard (BS EN 60669-1) 3x avec bascules Disjoncteur



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2830 01	10		29	4010337830016
 blanc brillant	2830 03	10		29	4010337830030
 anthracite	2830 28	10	26,49	29	4010337830283
 teinte alu	2830 26	10	30,13	29	4010337830269
 noir mat	2830 005	10	30,13	29	4010337038580
 gris mat	2830 015	10		29	4010337087113
 Acier inoxydable (laqué)	2830 600	10		29	4010337022022

Caractéristiques techniques

Profondeur d'encastrement:	25 mm
section de raccordement - Pour les conducteurs jusqu'à:	2,5mm ²
Puissance nominale:	100 W charge LED (IEC 60669)