








**Bouton-poussoir à bascule 3x 10 A 250 V~ avec bascules
Contact NO à 1 pôle**

Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2844 01	10	35,86	29	4010337082033
 blanc brillant	2844 03	10	35,86	29	4010337082040
 anthracite	2844 28	10	38,46	29	4010337082064
 teinte alu	2844 26	10	42,29	29	4010337082057
 noir mat	2844 005	10	42,29	29	4010337037903
 gris mat	2844 015	10	42,29	29	4010337087182
 acier inoxydable (laqué)	2844 600	10	45,92	29	4010337021957

Caractéristiques

- Avec bornes vissées.

Caractéristiques techniques

Profondeur d'encastrement: 25 mm

section de raccordement
- Pour les conducteurs jusqu'à: 2,5mm²

Indications

- Uniquement pour fixation par vis.
