








**Bouton-poussoir à bascule 3x 10 A 250 V~ avec bascules
Contact NO à 1 pôle**



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 2844 01 | 10 | 35,86 | 29 | 4010337082033 |
|  blanc brillant | 2844 03 | 10 | 35,86 | 29 | 4010337082040 |
|  anthracite | 2844 28 | 10 | 38,46 | 29 | 4010337082064 |
|  teinte alu | 2844 26 | 10 | 42,29 | 29 | 4010337082057 |
|  noir mat | 2844 005 | 10 | 42,29 | 29 | 4010337037903 |
|  gris mat | 2844 015 | 10 | 42,29 | 29 | 4010337087182 |
|  acier inoxydable (laqué) | 2844 600 | 10 | 45,92 | 29 | 4010337021957 |

Caractéristiques

- Avec bornes vissées.

Caractéristiques techniques

Profondeur d'encastrement: 25 mm

section de raccordement
- Pour les conducteurs jusqu'à: 2,5mm²

Indications

- Uniquement pour fixation par vis.
