

Interrupteur-poussoir 10 AX 250 V~avec bascule droite 2x Commutateur va-et-vient double



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	2861 201	1/5	40,02	01	4010337065883
 blanc satiné	2861 27	1/5	40,02	01	4010337053286
 anthracite	2861 28	1/5	40,54	11	4010337053293
 teinte alu	2861 26	1/5	43,74	11	4010337053279
 acier inoxydable	2861 600	1/5	50,74	11	4010337021209

Caractéristiques techniques

Profondeur d'encastrement

- 2860 ...:	28 mm
- 2861 ...:	32 mm

section de raccordement

- pour conducteurs rigides et flexibles jusqu'à:	2,5mm ²
--	--------------------

Puissance nominale

- LEDi/ CFLi:	100 W
---------------	-------

Indications

- A condition que la livraison soit possible.
