









Bascule avec symbole Porte



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3287 01	1	5,65	01	4010337039846
 blanc brillant	3287 03	10	5,65	01	4010337039853
 blanc satiné	3287 27	5	5,65	01	4010337039877
 anthracite	3287 28	1	6,14	11	4010337039884
 teinte alu	3287 26	1	9,29	11	4010337039860
 noir mat	3287 005	1	9,29	11	4010337067931
 gris mat	3287 015	1	9,29	11	4010337110484
 acier inoxydable	3287 600	1	16,40	11	4010337045250