









## Bascule avec fenêtre de contrôle



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3290 01	1	5,64	01	4010337041610
 blanc brillant	3290 03	10/100	5,64	01	4010337041627
 blanc satiné	3290 27	10	5,64	01	4010337041641
 anthracite	3290 28	10	6,14	11	4010337041658
 teinte alu	3290 26	1	9,29	11	4010337041634
 noir mat	3290 005	10	9,29	11	4010337067047
 gris mat	3290 015	10	9,29	11	4010337110491
 acier inoxydable	3290 600	1/5	16,37	11	4010337045403