









Bascule 2x avec symbole de flèche



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3294 01	10	10,50	01	4010337041191
 blanc brillant	3294 03	10/100	10,50	01	4010337041429
 blanc satiné	3294 27	10	10,50	01	4010337041443
 anthracite	3294 28	10	11,06	11	4010337041450
 teinte alu	3294 26	10	14,24	11	4010337041436
 noir mat	3294 005	10	14,68	11	4010337065746
 gris mat	3294 015	10	14,68	11	4010337110507
 acier inoxydable	3294 600	10	21,28	11	4010337045380