









## Bascule 2x avec symbole de flèche



| Spécification  | Réf.     | UV.    | EUR/pièce HTVA | SP | EAN           |
|--|----------|--------|----------------|----|---------------|
|  blanc crème brillant | 3294 01  | 10     | 10,50          | 01 | 4010337041191 |
|  blanc brillant     | 3294 03  | 10/100 | 10,50          | 01 | 4010337041429 |
|  blanc satiné       | 3294 27  | 10     | 10,50          | 01 | 4010337041443 |
|  anthracite         | 3294 28  | 10     | 11,06          | 11 | 4010337041450 |
|  teinte alu         | 3294 26  | 10     | 14,24          | 11 | 4010337041436 |
|  noir mat           | 3294 005 | 10     | 14,68          | 11 | 4010337065746 |
|  gris mat           | 3294 015 | 10     | 14,68          | 11 | 4010337110507 |
|  acier inoxydable   | 3294 600 | 10     | 21,28          | 11 | 4010337045380 |