










Bascule 2x



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3295 01	10	7,66	01	4010337040811
 blanc brillant	3295 03	10/100	7,66	01	4010337040828
 blanc satiné	3295 27	10	7,66	01	4010337040842
 anthracite	3295 28	10	8,23	11	4010337040859
 teinte alu	3295 26	10	11,41	11	4010337040835
 noir mat	3295 005	10	11,41	11	4010337065616
 gris mat	3295 015	10	11,41	11	4010337110514
 acier inoxydable	3295 600	1/5	18,43	11	4010337045267