










Bouton à bascule



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3296 01	10	4,03	21	4010337039341
 blanc brillant	3296 03	10/100	4,03	21	4010337039358
 blanc satiné	3296 27	10/100	4,03	21	4010337039372
 anthracite	3296 28	10/100	4,74	11	4010337039389
 teinte alu	3296 26	10	7,93	11	4010337039365
 noir mat	3296 005	10	7,93	11	4010337065593
 gris mat	3296 015	10	7,93	11	4010337110521
 acier inoxydable	3296 600	10	14,96	11	4010337043867