









## Bascule 2x avec symboles de flèche



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3297 01	1	10,50	01	4010337065821
 blanc brillant	3297 03	10	10,50	01	4010337065838
 blanc satiné	3297 27	10	10,50	01	4010337065869
 anthracite	3297 28	10	11,06	11	4010337065890
 teinte alu	3297 26	1	14,24	11	4010337065852
 noir mat	3297 005	10	14,24	11	4010337065814
 gris mat	3297 015	1	14,24	11	4010337110538