









## Bascule droite



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	3496 03	10	4,03	01	4010337121664
 blanc satiné	3496 27	10	4,03	01	4010337066101
 anthracite	3496 28	10	4,74	11	4010337066262
 teinte alu	3496 26	1	7,93	11	4010337065999
 noir mat	3496 005	10	7,93	11	4010337065944
 gris mat	3496 015	1	7,93	11	4010337110590
 acier inoxydable	3496 600	1/5	14,96	11	4010337066279