








## Bascule avec symbole et zone d'inscription Sonnette



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3673 01	1	9,31	01	4010337039990
 blanc brillant	3673 03	10	9,31	01	4010337040040
 blanc satiné	3673 27	10	9,31	01	4010337040200
 anthracite	3673 28	5	9,89	11	4010337040217
 teinte alu	3673 26	1	13,05	11	4010337040057
 noir mat	3673 005	1	13,05	11	4010337067955
 gris mat	3673 015	1	13,05	11	4010337110576

### Etendue de la livraison

- Étiquette vierge fournie.