

**Prise SCHUKO 16 A 250 V~avec zone d'inscription
System 55**



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	4457 01	1/5	10,99	01	4010337093244
 blanc brillant	4457 03	1/5	10,99	01	4010337093268
 blanc satiné	4457 27	1/5	10,99	01	4010337093329
 anthracite	4457 28	1/5	12,25	11	4010337093336
 teinte alu	4457 26	1/5	16,80	11	4010337093312
 noir mat	4457 005	1/5	16,80	11	4010337093237
 gris mat	4457 015	1/5	16,80	11	4010337093251
 acier inoxydable (laqué)	4457 600	1/5	24,97	11	4010337093343

Caractéristiques techniques

Profondeur d'encastrement: 31 mm

section de raccordement

- Pour les conducteurs de: 1,5 mm² à 2,5 mm²

Etendue de la livraison

- Une étiquette « EDV » est jointe.
-