









Prise SCHUKO 16 A 250 V~avec zone d inscription System 55



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 4457 01 | 1/5 | 11,34 | 01 | 4010337093244 |
|  blanc brillant | 4457 03 | 1/5 | 11,34 | 01 | 4010337093268 |
|  blanc satiné | 4457 27 | 1/5 | 11,34 | 01 | 4010337093329 |
|  anthracite | 4457 28 | 1/5 | 12,64 | 11 | 4010337093336 |
|  teinte alu | 4457 26 | 1/5 | 17,34 | 11 | 4010337093312 |
|  noir mat | 4457 005 | 1/5 | 17,34 | 11 | 4010337093237 |
|  gris mat | 4457 015 | 1/5 | 17,34 | 11 | 4010337093251 |
|  acier inoxydable (laqué) | 4457 600 | 1/5 | 25,77 | 11 | 4010337093343 |

Caractéristiques techniques

| | |
|---|---|
| Profondeur d'encastrement: | 31 mm |
| section de raccordement - Pour les conducteurs de: | 1,5 mm ² à 2,5 mm ² |

Les illustrations sont similaires et peuvent différer de l'original.
Prix valables pour le pays : Belgique avec le prix actuel 01/25.

Etendue de la livraison

- Une étiquette « EDV » est jointe.
