









Prise SCHUKO 16 A 250 V~avec zone d inscription System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	4457 01	1/5	10,99	01	4010337093244
 blanc brillant	4457 03	1/5	10,99	01	4010337093268
 blanc satiné	4457 27	1/5	10,99	01	4010337093329
 anthracite	4457 28	1/5	12,25	11	4010337093336
 teinte alu	4457 26	1/5	16,80	11	4010337093312
 noir mat	4457 005	1/5	16,80	11	4010337093237
 gris mat	4457 015	1/5	16,80	11	4010337093251
 acier inoxydable (laqué)	4457 600	1/5	24,97	11	4010337093343

Caractéristiques techniques

Profondeur d'encastrement:	31 mm
section de raccordement - Pour les conducteurs de:	1,5 mm ² à 2,5 mm ²

Les illustrations sont similaires et peuvent différer de l'original.
Prix valables pour le pays : Belgique avec le prix actuel 01/24.

Etendue de la livraison

- Une étiquette « EDV » est jointe.
