









## Module rapporté de commande System 3000 2x



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5362 01	1/5	40,87	02	4010337063841
 blanc brillant	5362 03	1/5	40,87	02	4010337063858
 blanc satiné	5362 27	1	40,87	02	4010337063896
 anthracite	5362 28	1/5	43,66	02	4010337063902
 teinte alu	5362 26	1	48,08	02	4010337063889
 noir mat	5362 005	1/5	48,08	02	4010337063919
 gris mat	5362 015	1/5	48,08	02	4010337087229
 acier inoxydable	5362 600	1	56,06	02	4010337063926

### Caractéristiques techniques

Température ambiante: -20 °C à +45 °C