










Bascule 2x sans impression avec fenêtre de contrôle System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5369 01	1/5	10,52	02	4010337460534
 blanc brillant	5369 03	1/5	10,52	02	4010337460589
 blanc satiné	5369 27	1/5	10,52	02	4010337063650
 anthracite	5369 28	1/5	13,30	02	4010337063643
 teinte alu	5369 26	1/5	15,20	02	4010337063711
 noir mat	5369 005	1/5	15,20	02	4010337063629
 gris mat	5369 015	1/5	15,20	02	4010337087267
 acier inoxydable	5369 600	1	18,42	02	4010337063568

Caractéristiques

- Bascules de commande sans impression comme remplacement pour les bascules originales marquées avec des symboles.
 - Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
-

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-