

Bascule 2x sans impression
System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5370 01	1/5	8,35	02	4010337108498
 blanc brillant	5370 03	1/5	8,35	02	4010337108511
 blanc satiné	5370 27	1/5	8,35	02	4010337108535
 anthracite	5370 28	1/5	11,43	02	4010337108542
 teinte alu	5370 26	1/5	13,48	02	4010337108528
 noir mat	5370 005	1/5	13,48	02	4010337108474
 gris mat	5370 015	1/5	13,48	02	4010337108481
 acier inoxydable	5370 600	1/5	17,34	02	4010337108559

Caractéristiques

- Bascules de commande sans impression comme remplacement pour les bascules originales marquées avec des symboles.
 - Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
-

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-