










## Bascule 2x avec symboles de flèche et fenêtre de contrôle System 55



| Spécification   | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5386 01  | 1/5 | 12,93          | 02 | 4010337111672 |
|  blanc brillant      | 5386 03  | 1/5 | 12,93          | 02 | 4010337111689 |
|  blanc satiné        | 5386 27  | 1/5 | 12,93          | 02 | 4010337111696 |
|  anthracite          | 5386 28  | 1/5 | 15,68          | 02 | 4010337111702 |
|  teinte alu          | 5386 26  | 1/5 | 17,60          | 02 | 4010337111719 |
|  noir mat            | 5386 005 | 1/5 | 17,60          | 02 | 4010337111726 |
|  gris mat            | 5386 015 | 1/5 | 17,60          | 02 | 4010337111733 |
|  acier inoxydable    | 5386 600 | 1/5 | 20,95          | 02 | 4010337111740 |

## Caractéristiques

- Bascules de commande en remplacement des bascules originales marquées avec des symboles.
  - Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
- 

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-