










## Bascule 1x avec symboles de flèche et fenêtre de contrôle System 55



| Spécification   | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5388 01  | 1/5 | 7,19           | 02 | 4010337111856 |
|  blanc brillant      | 5388 03  | 1/5 | 7,19           | 02 | 4010337111863 |
|  blanc satiné        | 5388 27  | 1/5 | 7,19           | 02 | 4010337111870 |
|  anthracite          | 5388 28  | 1/5 | 10,17          | 02 | 4010337111887 |
|  teinte alu          | 5388 26  | 1/5 | 11,97          | 02 | 4010337111894 |
|  noir mat            | 5388 005 | 1/5 | 11,97          | 02 | 4010337111900 |
|  gris mat            | 5388 015 | 1/5 | 11,97          | 02 | 4010337111917 |
|  acier inoxydable    | 5388 600 | 1/5 | 17,36          | 02 | 4010337111924 |

## Caractéristiques

- Bascule de commande en remplacement de la bascule d'origine marquée de symboles.

---

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.

---