








## Systeme 106 Couv. touche d appel p. module touche d appel 2x



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 acier inoxydable	5542 920	1	43,04	20	4010337022688
 Aluminium	5542 926	1	35,95	20	4010337022671
 blanc trafic (laqué)	5542 902	1	31,64	20	4010337022664
 Acier inoxydable V4A	5542 914	1	56,24	20	4010337092087
 bronze	5542 921	1	56,24	20	4010337100959
 noir mat	5542 925	1	56,24	20	4010337100799

### Dimensions en mm

2x: H 52,0 B 105,5