







## Touche d'appel System 106 avec zone d'inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 acier inoxydable	5547 920	1	41,58	20	4010337022770
 aluminium	5547 926	1	29,80	20	4010337022763
 blanc trafic (laqué)	5547 902	1	14,92	20	4010337022756
 acier inoxydable V4A	5547 914	1	56,30	20	4010337092063
 bronze	5547 921	1	56,30	20	4010337100935
 noir mat	5547 925	1	56,30	20	4010337100775

### Indications

- Marquage professionnel via le service de marquage Girawww.beschriftung.gira.de/fr/.

### Dimensions en mm

H 25,3      B 105,5