







## Touche d'appel System 106 avec zone d'inscription



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  acier inoxydable       | 5547 920 | 1   | 41,58          | 20 | 4010337022770 |
|  aluminium            | 5547 926 | 1   | 29,80          | 20 | 4010337022763 |
|  blanc trafic (laqué) | 5547 902 | 1   | 14,92          | 20 | 4010337022756 |
|  acier inoxydable V4A | 5547 914 | 1   | 56,30          | 20 | 4010337092063 |
|  bronze               | 5547 921 | 1   | 56,30          | 20 | 4010337100935 |
|  noir mat             | 5547 925 | 1   | 56,30          | 20 | 4010337100775 |

### Indications

- Marquage professionnel via le service de marquage Gira [www.beschriftung.gira.de/fr/](http://www.beschriftung.gira.de/fr/).

### Dimensions en mm

H 25,3      B 105,5