








Touche d appel inscriptible System 106



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  acier inoxydable | 5549 920 | 1 | 51,00 | 20 | 4010337022800 |
|  aluminium | 5549 926 | 1 | 39,22 | 20 | 4010337022794 |
|  blanc trafic (laqué) | 5549 902 | 1 | 34,43 | 20 | 4010337022787 |
|  acier inoxydable V4A | 5549 914 | 1 | 69,08 | 20 | 4010337092056 |
|  bronze | 5549 921 | 1 | 69,08 | 20 | 4010337100928 |
|  noir mat | 5549 925 | 1 | 69,08 | 20 | 4010337100768 |

Indications

- Ce produit peut uniquement être commandé via le service de marquage Gira.
- Marquage professionnel via le service de marquage Gira www.beschriftung.gira.de/fr/.

Etendue de la livraison

- Avec inscription laser individuelle.

Dimensions en mm

H 25,3

B 105,5
