








Anneau de support jack modulaire 2x Anneau de support MJ-01 à MJ-10



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|---|---------|-----|----------------|----|---------------|
|  Anneau de support MJ-01 | 5601 00 | 10 | 7,04 | 01 | 4010337460015 |
|  Anneau de support MJ-02 | 5602 00 | 10 | 7,04 | 01 | 4010337460022 |
|  Anneau de support MJ-03 | 5603 00 | 10 | 7,04 | 01 | 4010337460039 |
|  Anneau de support MJ-04 | 5604 00 | 10 | 7,04 | 01 | 4010337460046 |
|  Anneau de support MJ-05 | 5605 00 | 10 | 7,04 | 01 | 4010337460053 |
|  Anneau de support MJ-06 | 5606 00 | 10 | 7,04 | 01 | 4010337460060 |
|  Anneau de support MJ-07 | 5607 00 | 10 | 7,04 | 01 | 4010337460077 |
|  Anneau de support MJ-08 | 5608 00 | 10 | 7,04 | 01 | 4010337460084 |
|  Anneau de support MJ-09 | 5609 00 | 10 | 7,04 | 01 | 4010337460091 |



Anneau de support MJ-10

5610 00

10

7,04

01

4010337460107

Indications

- Uniquement pour fixation par vis.
- Convient pour l'installation en goulotte.

Dimensions en mm

| | | |
|---------------------|--------|--------|
| MJ-01, MJ02, MJ-07: | B 14,8 | H 19,5 |
| MJ-03: | B 14,8 | H 20,0 |
| MJ-04, MJ-09: | B 14,8 | H 19,3 |
| MJ-05: | B 16,7 | H 17,3 |
| MJ-06: | B 15,9 | H 18,3 |
| MJ-08: | B 14,8 | H 19,0 |
| MJ-10: | B 16,1 | H 18,5 |
