










Bascule pour jeu de bascules 2x pour Tastsensor 4



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  aluminium blanc brillant (laqué) | 8332 903 | 1 | 55,07 | 06 | 4010337098713 |
|  aluminium blanc satiné (laqué) | 8332 927 | 1 | 55,07 | 06 | 4010337098737 |
|  aluminium anthracite (laqué) | 8332 928 | 1 | 55,07 | 06 | 4010337098676 |
|  aluminium (anodisé) | 8332 17 | 1 | 43,48 | 06 | 4010337096979 |
|  aluminium noir mat (laqué) | 8332 905 | 1 | 55,07 | 06 | 4010337098690 |
|  aluminium gris mat (laqué) | 8332 915 | 1 | 55,07 | 06 | 4010337098652 |
|  aluminium noir (anodisé) | 8332 126 | 1 | 43,48 | 06 | 4010337096993 |
|  bronze | 8332 38 | 1 | 92,75 | 06 | 4010337098751 |
|  verre blanc | 8332 12 | 1 | 43,48 | 06 | 4010337097792 |

| | | | | | | |
|---|------------------|----------|---|-------|----|---------------|
|  | verre noir | 8332 05 | 1 | 43,48 | 06 | 4010337098027 |
|  | acier inoxydable | 8332 219 | 1 | 75,36 | 06 | 4010337097334 |