











Bascule pour jeu de bascules 4x pour Tastsensor 4



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  aluminium blanc brillant (laqué) | 8334 903 | 1 | 43,48 | 06 | 4010337098720 |
|  aluminium blanc satiné (laqué) | 8334 927 | 1 | 43,48 | 06 | 4010337098744 |
|  aluminium anthracite (laqué) | 8334 928 | 1 | 43,48 | 06 | 4010337098683 |
|  aluminium (anodisé) | 8334 17 | 1 | 31,89 | 06 | 4010337096986 |
|  aluminium noir mat (laqué) | 8334 905 | 1 | 43,48 | 06 | 4010337098706 |
|  aluminium gris mat (laqué) | 8334 915 | 1 | 43,48 | 06 | 4010337098669 |
|  aluminium noir (anodisé) | 8334 126 | 1 | 31,89 | 06 | 4010337097228 |
|  bronze | 8334 38 | 1 | 75,36 | 06 | 4010337098775 |
|  verre blanc | 8334 12 | 1 | 31,89 | 06 | 4010337098010 |

| | | | | | |
|--|---------|---|-------|----|---------------|
|  verre noir | 8334 05 | 1 | 31,89 | 06 | 4010337098034 |
|--|---------|---|-------|----|---------------|

| | | | | | |
|--|----------|---|-------|----|---------------|
|  acier inoxydable | 8334 219 | 1 | 57,97 | 06 | 4010337097785 |
|--|----------|---|-------|----|---------------|
