

## Cadre de finition Gira Standard 55 blanc brillant



| Spécification                                                                                                | Réf.    | UV.    | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------|---------|--------|----------------|----|---------------|
|  1x                        | 0211 03 | 10/100 | 3,21           | 21 | 4010337211037 |
|  1,5x                     | 1001 03 | 10     | 4,33           | 01 | 4010337881308 |
|  2x                       | 0212 03 | 10/100 | 5,48           | 21 | 4010337212034 |
|  2x sans nervure centrale | 1002 03 | 10     | 4,05           | 01 | 4010337001607 |
|  3x                       | 0213 03 | 10/100 | 9,66           | 01 | 4010337213031 |
|  4x                       | 0214 03 | 1/5    | 16,71          | 01 | 4010337214038 |
|  5x                       | 0215 03 | 1/5    | 27,49          | 01 | 4010337215035 |

### Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.

## Indications

- Convient également pour installations en goulotte.
  - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.
-