








Prise British Standard (BS 1363) 13 A 250 V~ avec shutter System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2776 01	10	18,74	29	4010337079347
 blanc brillant	2776 03	10	18,74	29	4010337079354
 anthracite	2776 28	10	21,46	29	4010337079378
 teinte alu	2776 26	10	25,65	29	4010337079361
 noir mat	2776 005	10	25,65	29	4010337037774
 gris mat	2776 015	10	25,65	29	4010337086352
 acier inoxydable (laqué)	2776 600	10	29,48	29	4010337022077

Caractéristiques

- Avec bornes vissées.

Caractéristiques techniques

Profondeur de montage: 17 mm

Indications

- Uniquement pour fixation par vis.
 - Autres fonctions et variantes également disponibles sur demande pour le boîtier BS de 80.
-