


**Prise British Standard (BS 1363) 13 A 250 V~ branchée, avec shutter
System 55**



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2778 01	10	21,64	29	4010337079477
 blanc brillant	2778 03	10	21,64	29	4010337079484
 blanc satiné	2778 27	10	21,64	29	4010337036418
 anthracite	2778 28	10	24,35	29	4010337079507
 teinte alu	2778 26	10	28,53	29	4010337079491
 noir mat	2778 005	10	28,53	29	4010337037750
 gris mat	2778 015	10	28,53	29	4010337086390
 acier inoxydable (laqué)	2778 600	10	32,42	29	4010337022091

Caractéristiques

- Avec bornes vissées.
-

Caractéristiques techniques

Profondeur de montage: 20 mm

Indications

- Uniquement pour fixation par vis.
 - Autres fonctions et variantes également disponibles sur demande pour le boîtier BS de 80.
-