


**Bascule avec symbole**  
**Porte**



| Spécification   | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 3287 01  | 1   | 6,05           | 01 | 4010337039846 |
|  blanc brillant      | 3287 03  | 10  | 6,05           | 01 | 4010337039853 |
|  blanc satiné        | 3287 27  | 5   | 6,05           | 01 | 4010337039877 |
|  anthracite          | 3287 28  | 1   | 6,58           | 11 | 4010337039884 |
|  teinte alu          | 3287 26  | 1   | 9,95           | 11 | 4010337039860 |
|  noir mat            | 3287 005 | 1   | 9,95           | 11 | 4010337067931 |
|  gris mat            | 3287 015 | 1   | 9,95           | 11 | 4010337110484 |
|  acier inoxydable    | 3287 600 | 1   | 17,56          | 11 | 4010337045250 |