


## Bascule avec fenêtre de contrôle et zone d'inscription



| Spécification                                                                                          | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 3670 01  | 1   | 9,95           | 01 | 4010337041740 |
|  blanc brillant     | 3670 03  | 1   | 9,95           | 01 | 4010337041757 |
|  blanc satiné       | 3670 27  | 1   | 9,95           | 01 | 4010337041771 |
|  anthracite         | 3670 28  | 1   | 10,59          | 11 | 4010337041788 |
|  teinte alu         | 3670 26  | 1   | 13,96          | 11 | 4010337041764 |
|  noir mat           | 3670 005 | 1   | 13,96          | 11 | 4010337067078 |
|  gris mat           | 3670 015 | 1   | 13,96          | 11 | 4010337110569 |

## Etendue de la livraison

- Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.