

## Module rapporté de commande System 3000 2x



| Spécification                                                                                          | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5362 01  | 1/5 | 43,87          | 02 | 4010337063841 |
|  blanc brillant     | 5362 03  | 1/5 | 43,87          | 02 | 4010337063858 |
|  blanc satiné       | 5362 27  | 1/5 | 43,87          | 02 | 4010337063896 |
|  anthracite         | 5362 28  | 1/5 | 46,86          | 02 | 4010337063902 |
|  teinte alu         | 5362 26  | 1   | 51,60          | 02 | 4010337063889 |
|  noir mat           | 5362 005 | 1/5 | 51,60          | 02 | 4010337063919 |
|  gris mat           | 5362 015 | 1/5 | 51,60          | 02 | 4010337087229 |
|  acier inoxydable   | 5362 600 | 1/5 | 60,17          | 02 | 4010337063926 |

## Caractéristiques techniques

Température ambiante: -20 °C à +45 °C