

Interruttore a bilanciere British Standard (BS EN 60669-1) 20 AX 250 V~ con bilanciere
Interruttore a 2 poli

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2836 01	10	38,99	29	4010337078944
 bianco puro brillante	2836 03	10	38,99	29	4010337078951
 antracite	2836 28	10	39,71	29	4010337078975
 color alluminio	2836 26	1	42,87	29	4010337078968
 nero opaco	2836 005	10	42,87	29	4010337038566
 grigio opaco	2836 015	10	42,87	29	4010337087144
 acciaio inox	2836 600	10	49,81	29	4010337021933

Caratteristiche

- Con morsetti a vite.

Dati tecnici

Profondità di montaggio:	24 mm
Sezione dei conduttori - per conduttori fino a:	2 x 4 mm ² o 1 x 6 mm ²

Avvisi

- Solo per fissaggio a viti.
 - BS EN 60669-1.
-