


Modulo calotta dati per Modular Jack AMP



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 2 moduli	0039 00	5/25	6,12	01	4010337039006

Avvisi

- Adatto per:

AMP a 6 poli 1116603--1 toolless cat.3

AMP 8 poli 1116515-1 cat.5e schermato

AMP 8 poli 1116604-1 toolless cat.5e non schermato

AMP 8 poli 1339015-1 toolless cat.5e schermato

AMP 8 poli 1375055-1 SL cat.6 non schermato

AMP 8 poli 1375188-1 SL cat.6 schermatosnap in jack RJ45

Kannegieter BICC Brand Rex

Krone Inline RJ45 schermato/non schermato

AMP SL serie RJ45 jack cat.5E

AMP TWIST-7AS SL jack 8 poli 1711441-1 schermato cat.7A

AMP TWIST-7AS SL jack 8 poli 1711437-1 schermato cat.7A

AMP TWIST-6S SL jack 8 poli 1711160-1 schermato cat.6

AMP TWIST-6S SL jack 8 poli 1711342-1 schermato cat.6

AMP TWIST-6AS SL jack 8 poli 1711592-1 schermato cat.6A

AMP TWIST-6AS SL jack 8 poli 1711716-1 schermato cat.6A

AMP LC LWL adattatore duplex

AMP MT RJ LWL duplex.

- Seconda apertura chiudibile.