









## Interruttore a pulsante 10 AX 250 V~con bilanciere diritto Deviatore universale



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco puro brillante	0121 201	1/5	17,70	01	4010337052692
 bianco puro satinato	0121 27	1/5	17,70	01	4010337029311
 antracite	0121 28	1/5	18,20	11	4010337029335
 color alluminio	0121 26	1	21,40	11	4010337029328
 nero opaco	0121 005	1	21,40	11	4010337037972
 grigio opaco	0121 015	1	21,40	11	4010337077091
 acciaio inox	0121 600	1/5	28,42	11	4010337021261

### Dati tecnici

Profondità di montaggio:	28 mm
Sezione dei conduttori - per conduttori rigidi e flessibili fino a:	2,5mm <sup>2</sup>
Potenza nominale - LEDi/CFLi:	100 W

---

## Avvisi

- Soggetto a disponibilità.

---