

**Interruttore di controllo a pulsante 10 AX 250 V~ con bilanciere
Interruttore a 2 poli**

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0122 01	1/5	45,00	01	4010337122012
 bianco puro brillante	0122 03	1/5	45,00	01	4010337122036
 bianco puro satinato	0122 27	1/5	45,00	01	4010337122272
 antracite	0122 28	1/5	45,55	11	4010337122289
 color alluminio	0122 26	1/5	48,71	11	4010337122265
 nero opaco	0122 005	1/5	48,71	11	4010337037934
 acciaio inox	0122 600	1/5	55,78	11	4010337021773

Dati tecnici

Profondità di montaggio:	28 mm
Sezione dei conduttori - per conduttori rigidi e flessibili fino a:	2,5mm ²
Potenza nominale - LEDi/CFLi:	100 W

Avvisi

- Collegabile anche illuminato.

Contenuto della fornitura

- L'elemento di lampada fluorescente 230 V~ 1,5 mA è in dotazione.
-