










Interruttore a pulsante 10 AX 250 V~ con bilanciere Invertitore



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  bianco crema brillante | 0127 01 | 1/5 | 28,29 | 01 | 4010337127017 |
|  bianco puro brillante | 0127 03 | 1/5 | 28,29 | 01 | 4010337127031 |
|  bianco puro satinato | 0127 27 | 1/5 | 28,29 | 01 | 4010337127277 |
|  antracite | 0127 28 | 1/5 | 28,85 | 11 | 4010337127284 |
|  color alluminio | 0127 26 | 1/5 | 32,03 | 11 | 4010337127260 |
|  nero opaco | 0127 005 | 1/5 | 32,03 | 11 | 4010337037989 |
|  grigio opaco | 0127 015 | 1/5 | 32,03 | 11 | 4010337077169 |
|  acciaio inox | 0127 600 | 1/5 | 39,06 | 11 | 4010337021759 |

Dati tecnici

Profondità di montaggio: 28 mm

Sezione dei conduttori
- per conduttori rigidi e flessibili fino a: 2,5mm²

Le illustrazioni sono simili all'originale e possono differire da esso.
Prezzi validi per Italia con aggiornamento prezzi 11/23.

Potenza nominale

- LEDi/CFLi:

100 W

Avvisi

- Soggetto a disponibilità.
