









Interruttore a pulsante 10 AX 250 V~ con bilanciere Invertitore



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0127 01	1/5	28,29	01	4010337127017
 bianco puro brillante	0127 03	1/5	28,29	01	4010337127031
 bianco puro satinato	0127 27	1/5	28,29	01	4010337127277
 antracite	0127 28	1/5	28,85	11	4010337127284
 color alluminio	0127 26	1/5	32,03	11	4010337127260
 nero opaco	0127 005	1/5	32,03	11	4010337037989
 grigio opaco	0127 015	1/5	32,03	11	4010337077169
 acciaio inox	0127 600	1/5	39,06	11	4010337021759

Dati tecnici

Profondità di montaggio: 28 mm

Sezione dei conduttori
- per conduttori rigidi e flessibili fino a: 2,5mm²

Le illustrazioni sono simili all'originale e possono differire da esso.
Prezzi validi per Italia con aggiornamento prezzi 11/23.

Potenza nominale
- LEDi/CFLi:

100 W

Avvisi

- Soggetto a disponibilità.
