


**Interruttore a pulsante 10 AX 250 V~ con bilanciare 2 moduli
Deviatore 2 moduli**



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0128 01	1/5	40,02	01	4010337128014
 bianco puro brillante	0128 03	1/5	40,02	01	4010337128038
 bianco puro satinato	0128 27	1/5	40,02	01	4010337128274
 antracite	0128 28	1/5	40,54	11	4010337128281
 color alluminio	0128 26	1/5	43,74	11	4010337128267
 nero opaco	0128 005	1/5	43,74	11	4010337038030
 grigio opaco	0128 015	1/5	43,74	11	4010337077176
 acciaio inox	0128 600	1/5	50,74	11	4010337021797

Dati tecnici

Profondità di montaggio
- 0125 ...:

28 mm

- 0128 ...: 32 mm

Sezione dei conduttori
- per conduttori rigidi e flessibili fino a: 2,5mm²

Potenza nominale
- LEDi/CFLi: 100 W
