









**Pulsante 10 A 250 V~ con bilanciere diritto  
Commutatore a 1 polo**

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco puro brillante	0130 201	1/5	19,18	01	4010337066064
 bianco puro satinato	0130 27	1/5	19,18	01	4010337029434
 antracite	0130 28	1/5	19,91	11	4010337029458
 color alluminio	0130 26	1/5	23,08	11	4010337029441
 nero opaco	0130 005	1/5	23,08	11	4010337037910
 grigio opaco	0130 015	1/5	23,08	11	4010337077183
 acciaio inox	0130 600	1/5	29,95	11	4010337035947

**Dati tecnici**

Profondità di montaggio:	28 mm
Sezione dei conduttori - per conduttori rigidi e flessibili fino a:	2,5mm <sup>2</sup>

## Avvisi

- Soggetto a disponibilità.

---