








## Placca Gira E2 nero opaco



| Specifica   | Cod. ord. | UI  | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|-----|-----------------------|----|---------------|
|  1 modulo                         | 0211 09   | 10  | 12,14                 | 11 | 4010337036739 |
|  1,5 moduli                      | 1001 09   | 10  | 17,96                 | 11 | 4010337072775 |
|  2 moduli                        | 0212 09   | 10  | 18,43                 | 11 | 4010337036760 |
|  2 moduli senza costola centrale | 1002 09   | 10  | 18,43                 | 11 | 4010337036784 |
|  3 moduli                        | 0213 09   | 1/5 | 30,31                 | 11 | 4010337036821 |
|  4 moduli                        | 0214 09   | 1/5 | 49,23                 | 11 | 4010337036869 |
|  5 moduli                        | 0215 09   | 1/5 | 74,90                 | 11 | 4010337036906 |

### Avvisi

- Adatta anche per installazioni in canalina.
- Placca (1-5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.