







Placca Gira F100 bianco puro brillante



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 112	10	7,56	01	4010337043973
 2 moduli	0212 112	10	13,34	01	4010337044017
 2 moduli senza costola centrale	1002 112	10	13,34	01	4010337047094
 3 moduli	0213 112	1/5	21,54	01	4010337044031
 4 moduli	0214 112	1/5	34,67	01	4010337044055
 5 moduli	0215 112	1/5	52,96	01	4010337044079

Caratteristiche

- Infrangibile.

Avvisi

- In combinazione con la flangia di tenuta, adatta anche per il montaggio da incasso IP 44 (protezione dall'acqua).