







Placca Gira E1 bianco puro satinato



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  1 modulo | 0211 151 | 10 | 7,49 | 01 | 4010337126171 |
|  2 moduli | 0212 151 | 10 | 10,28 | 01 | 4010337126188 |
|  2 moduli senza costola centrale | 1002 151 | 1 | 10,28 | 01 | 4010337126195 |
|  3 moduli | 0213 151 | 1/5 | 18,76 | 01 | 4010337126218 |
|  4 moduli | 0214 151 | 1/5 | 30,30 | 01 | 4010337126225 |
|  5 moduli | 0215 151 | 1/5 | 46,23 | 01 | 4010337126232 |

Caratteristiche

- Infrangibile.

Avvisi

- Adatta anche per installazioni in canalina.
- Placca (1-5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.