








Placca Gira E2 color alluminio



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|--------|-----------------------|----|---------------|
|  1 modulo | 0211 25 | 10/100 | 12,14 | 11 | 4010337211259 |
|  1,5 moduli | 1001 25 | 10 | 17,96 | 11 | 4010337881346 |
|  2 moduli | 0212 25 | 10 | 18,43 | 11 | 4010337212256 |
|  2 moduli senza costola centrale | 1002 25 | 10 | 18,43 | 11 | 4010337002253 |
|  3 moduli | 0213 25 | 1/5 | 30,31 | 11 | 4010337213253 |
|  4 moduli | 0214 25 | 1/5 | 49,23 | 11 | 4010337214250 |
|  5 moduli | 0215 25 | 1/5 | 74,90 | 11 | 4010337215257 |

Avvisi

- Adatta anche per installazioni in canalina.
- Placca (1 - 5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.