








Placca Gira E2 nero opaco



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  1 modulo | 0211 09 | 10 | 12,14 | 11 | 4010337036739 |
|  1,5 moduli | 1001 09 | 10 | 17,96 | 11 | 4010337072775 |
|  2 moduli | 0212 09 | 10 | 18,43 | 11 | 4010337036760 |
|  2 moduli senza costola centrale | 1002 09 | 10 | 18,43 | 11 | 4010337036784 |
|  3 moduli | 0213 09 | 1/5 | 30,31 | 11 | 4010337036821 |
|  4 moduli | 0214 09 | 1/5 | 49,23 | 11 | 4010337036869 |
|  5 moduli | 0215 09 | 1/5 | 74,90 | 11 | 4010337036906 |

Avvisi

- Adatta anche per installazioni in canalina.
- Placca (1-5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.