








## Placca Gira E2 color alluminio



| Specifica   | Cod. ord. | UI     | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|--------|-----------------------|----|---------------|
|  1 modulo                         | 0211 25   | 10/100 | 12,14                 | 11 | 4010337211259 |
|  1,5 moduli                      | 1001 25   | 10     | 17,96                 | 11 | 4010337881346 |
|  2 moduli                        | 0212 25   | 10     | 18,43                 | 11 | 4010337212256 |
|  2 moduli senza costola centrale | 1002 25   | 10     | 18,43                 | 11 | 4010337002253 |
|  3 moduli                        | 0213 25   | 1/5    | 30,31                 | 11 | 4010337213253 |
|  4 moduli                        | 0214 25   | 1/5    | 49,23                 | 11 | 4010337214250 |
|  5 moduli                        | 0215 25   | 1/5    | 74,90                 | 11 | 4010337215257 |

### Avvisi

- Adatta anche per installazioni in canalina.
- Placca (1 - 5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.