








Placca Gira Standard 55 bianco puro satinato



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 04	10/100	2,99	21	4010337211044
 1,5 moduli	1001 04	10	4,04	01	4010337881315
 2 moduli	0212 04	10/100	5,12	21	4010337212041
 2 moduli senza costola centrale	1002 04	10	3,78	01	4010337002048
 3 moduli	0213 04	10/100	9,02	01	4010337213048
 4 moduli	0214 04	1/5	15,60	01	4010337214045
 5 moduli	0215 04	1/5	25,66	01	4010337215042

Caratteristiche

- Infrangibile.

Avvisi

- Adatta anche per installazioni in canalina.
 - Placca (1-5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.
-