








Placca Gira Standard 55 bianco puro satinato



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---------------------------------------------------------------------------------------------------------------------|-----------|--------|-----------------------|----|---------------|
|  1 modulo | 0211 04 | 10/100 | 3,09 | 21 | 4010337211044 |
|  1,5 moduli | 1001 04 | 10 | 4,17 | 01 | 4010337881315 |
|  2 moduli | 0212 04 | 10/100 | 5,28 | 21 | 4010337212041 |
|  2 moduli senza costola centrale | 1002 04 | 10 | 3,90 | 01 | 4010337002048 |
|  3 moduli | 0213 04 | 10/100 | 9,31 | 01 | 4010337213048 |
|  4 moduli | 0214 04 | 1/5 | 16,10 | 01 | 4010337214045 |
|  5 moduli | 0215 04 | 1/5 | 26,48 | 01 | 4010337215042 |

Caratteristiche

- Infrangibile.

Avvisi

- Adatta anche per installazioni in canalina.
 - Placca (1-5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.
-